

## Power Supplies

### **EN** User Manual

Updates and language specific user manuals are available on  
**[www.mascot.no/downloads/usermanuals](http://www.mascot.no/downloads/usermanuals)**



Bruksanvisning  
Käyttöohjeet  
Bedienungsanleitung  
Mode d'emploi  
Manual de instrucciones  
Istruzioni per l'uso



**MASCOT ELECTRONICS AS**  
P.O.Box 177, N-1601 Fredrikstad, NORWAY  
Phone: +47 69 36 43 00 • Telefax: +47 69 36 43 01  
E-mail: [sales@mascot.no](mailto:sales@mascot.no) • Web: [www.mascot.no](http://www.mascot.no)

Doc.no. 00010 - Part No. 017963 - 19.06.2019



## IMPORTANT SAFETY INSTRUCTIONS!



**TO REDUCE THE RISK OF FIRE AND ELECTRIC SHOCK:**

**READ THROUGH THESE INSTRUCTIONS PRIOR TO USING THE PRODUCT.**

**CAREFULLY FOLLOW THESE INSTRUCTIONS WHEN USING THE PRODUCT.**

**RETAIN THESE INSTRUCTIONS FOR FUTURE REFERENCE.**



**CAUTION! DOUBLE POLE / NEUTRAL FUSING!**



This product is designed for indoor use.  
(Not applicable to products marked "IP67")

**IP41 IP4X IP44**  **IP67**

A version of this product marked "IP41" may be available. This version is protected against ingress of solid objects larger than 1.0 mm and the effects of vertically falling drops of water according to standard EN/IEC 60529.

A version of this product marked "IP4X" or "IP40" may be available. This version is protected against ingress of solid objects larger than 1.0 mm.

A version of this product marked "IP44" may be available. This version is protected against ingress of solid objects larger than 1.0 mm and the effects of water splashed against the enclosure from any direction according to standard EN/IEC 60529.

A version of this product, marked with a symbol with two drops of water and/or "IP67", may be available. This version is filled with a potting

compound and is dust-tight and protected against the effects of temporary immersion in water according to standard EN/IEC 60529, but must not be immersed in water for longer periods of time.



Products marked with the "double square symbol" are double insulated (Insulation Class II). Products without this mark are Class I (relies on safety earth for protection).

**WARNING:** To avoid risk of electric shock, Class I products must only be connected to a supply mains with protective earth.



At the end of their service life electric and electronic equipment and their accessories shall not be discarded with the municipal waste but be disposed of using separate collection, treatment, recovery/recycling and environmentally sound disposal. This also applies to any potentially bio hazardous parts and accessories. If in doubt; contact your local authorities to determine the proper method.

Technical specifications for your product: See tables, the marking on the product or [www.mascot.no](http://www.mascot.no)

## Cautions to observe prior to use

- The intended use for this product is to charge a battery or a battery powered electrical accessory (NiCd/NiMH, Lead-Acid, Lithium-Ion or LiFePO<sub>4</sub> batteries) or to be used as a Power Supply to power an electrical accessory. Please see the marking on the product you have to verify the type of product you have and read the applicable instructions and technical specifications included with this manual.
- This product may be used by unskilled operators, under the condition that these instructions are followed.
- Unskilled operators may contact the supplier or manufacturer for assistance, if needed, in setting up, using or maintaining this product and to report unexpected operation or events.
- This appliance can be used by children aged from 8 years and above and persons with reduced physical, sensory or mental capabilities or lack of experience and knowledge if they have been given supervision or instruction concerning use of the appliance in a safe way and understand the hazards involved. Do not allow small children to handle this product while unattended as cables may represent a risk for strangulation and small parts may represent a risk for inhalation or swallowing.
- Do not allow animals to come into contact with this product. Some animals are known to cause damage to cables etc which may be a potential for risk of electric shock and excessive temperatures. Also, cables and small parts may represent a strangulation risk for the animal.
- If the product is equipped with a mains cord, please check that the cord is not damaged. If the cord is damaged, the product must not be used until the cord is replaced. Replacement should be carried out by qualified personnel.
- The mains socket outlet used should always be easily accessible to facilitate immediate removal of the products mains supply should an operational error occur during use. If the product has a detachable mains cord the appliance coupler may be used as a disconnect device.
- The product is "switched on" by inserting the mains plug into the mains socket and "switched off" by disconnecting the mains plug from the mains socket.
- The product may be connected to an IT type mains supply.
- For use in U.S.A.:
  - Be sure to use 125V 15A receptacle configuration before plugging in.
  - Use a UL817-standard compliant mains cord (plug type NEMA 1-15, cord type SJT or SVT).
- For use outside U.S.A.:

Use a mains cord compliant with the country specific requirements.
- The time from powering this product until its full function starts may exceed 15 seconds.
- Should an operational error or unexpected change in the performance occur during use; disconnect the product from the mains immediately by disconnecting the mains plug from the mains socket and contact the supplier or manufacturer (see contact details on the front of this document).
- When not in use please think about disconnecting the product from the mains. This will reduce the risk of hazards, reduce the products environmental impact and save electricity costs.
- To avoid overheating make sure there is sufficient room for the circulation of air around the product when in use. Do not cover it up.
- Even though this product complies with relevant safety standards it should not be in contact with human skin for long periods as some people may get allergies or injuries from long-term contact with moderate temperatures and/or plastic materials.
- Prior to using this product with accessories and/or interconnected equipment please carefully read its respective User Manuals.
- If the product is supplied with exchangeable output plugs, please see separate page for assembly.

- Output cables having a modular plug ( similar to a telephone connector) must never be connected to a telephone outlet.
- Products with a welded plastic housing or rated IP 67 are not repairable. For such products the supply cord cannot be replaced. If the cord is damaged the appliance should be scrapped. Please contact your supplier for replacement part.
- This product contains hazardous voltages and there are no user replaceable parts inside the product. Never attempt to remove the cover.
- **WARNING:** No modification of this equipment is allowed. Any repair/service should be carried out by qualified personnel who may get assistance by contacting the manufacturer or the manufacturer's agent.
- Products specified to have automatic polarity protection must be switched off if a battery is connected with reverse polarity. The protection will be automatically reset when the polarity has been corrected.
- In chargers specified to have a replaceable fuse as polarity protection the fuse must be replaced if the battery has been connected with reverse polarity. When replacing the fuse; a fuse of the same type and rating must be used.
- If the product is specified to comply with the standard for Medical Electrical Equipment (standards based on IEC60601-1) it complies with some of the requirements for medical electrical equipment and may be used in medical applications and hospital environments.
- The product must be kept away from sources of heat and may not be used in the vicinity of flammable anesthetic gases or in other environments with flammable or explosive atmosphere.
- If the product is specified to comply with the standard for Medical Electrical Equipment for Home Healthcare Environment (standard IEC60601-1-11) it may be used in medical applications used in a home healthcare

environment.

NOTE: Products relying on safety earth for protection (Class I) may not be used in home healthcare environment unless they are permanently wired to the building installation: Installation must only be carried out by qualified service personnel, following the below instructions:

- The protective earth conductor must be min. 0.75 mm<sup>2</sup>.
- Connect the protective earth conductor to the external protective earthing system.
- Verify that the protective earth terminal used is connected to the external protective earthing system.
- Verify the integrity of the external protective earthing system.
- This product converts the mains voltage to a safety extra low voltage. The output from products applying with 2MOPP insulation ( model names followed by "P") may be treated as Applied Part Type B or Type BF according to standard EN/IEC 60601-1 and may come in physical contact with a patient. The housing of the product shall not be allowed to contact the patient .
- This product must be operated in an environment within temperature range +5 to +40°C, humidity 15 - 93 % RH and atmospheric pressure 70 - 106 kPa (700 - 1060 hPa). If the product has recently been stored or transported at conditions outside this range; please wait for 30 minutes before operating the product.
- Expected service life of this product and accessories delivered with this product is three (3) years, if operated as indicated above. However; the guarantee times indicated in document "TERMS OF SALES AND DELIVERY FOR MASCOT AS" apply (available at [www.mascot.com](http://www.mascot.com)).
- Environmental parameters during transport and storage between uses: temperature range

-25 to +85 °C, humidity 15 - 93% RH NC and atmospheric pressure 70 - 106 kPa (700 - 1060 hPa).


- If stored for longer periods of time the environmental parameters should be within the temperature range +5 to +35°C, humidity range 10 - 75% RH NC and atmospheric pressure 70 - 106 kPa (700 - 1060 hPa) to the products expected service life.
- Expected shelf life of this product is one (1) year, if stored as indicated above.
- This product complies with the requirements to electromagnetic compatibility for medical electric equipment and for use in residential, office or light industrial environment but all electric products imply a potential for electromagnetic or other interference between the product and other devices. If such interference is suspected please disconnect the product from the mains and consult a qualified technician, your supplier or the manufacturer.
- No special maintenance procedure is required but if the product gets dusty or dirty it should be wiped clean using a dry cloth while the product is disconnected from the mains. No other maintenance should be necessary.
- For products having a plastic casing, please avoid any contact with lotions, oils, grease and solvents as most types of plastic may be degraded by such chemicals. Also make sure to position, operate and store such products away from UV-light and direct sunlight.
- Position, operate and store this product only under reasonable foreseeable environmental conditions with respect to magnetic fields, EM-fields, electrostatic discharges, pressure or variations in pressure, acceleration etc.
- If this product is used with or mounted in a vehicle it may only be used when the vehicle is not in use.
- When in use, position this product so that the label can be read – within 40 cm of the operator.
- Turn the product off and allow it's housing to cool down prior to moving it to another location.

## Instructions for using Power Supplies

Please follow cautions indicated above.

When the Power Supply is connected to the mains a LED might light. The Power Supply is then ready to use.

## How to connect exchangeable AC-plugs




### The following exchangeable AC plugs are available:

"EURO"	250V 2.5A (EN50075/IEC83 C5 II)
"US"	125V 2.5A (NEMA 1-15 / CSA-C22.2 No.42)
"UK"	250V 13A (BS 1363)
"AUS"	250V 10A (AS/NZS 3112)

Mains Cord Set is available on request if you wish your product to be "DeskTop"

## How to connect exchangeable DC-output plugs



1. To connect for desired polarity, both plug ends are clearly marked.
2. When connected, the female plug is also marked on each side to identify plug polarity.
3. Shows the center polarity of the plug.

## Electromagnetic Compatibility

In order to regulate the requirements for EMC (electromagnetic compatibility) with the aim of preventing unsafe product situations, the EMC EN60601-1-2 standard has been implemented. This standard defines the levels of immunity to electromagnetic interference as well as maximum levels of electromagnetic emissions for medical devices. Medical devices manufactured by Mascot have been tested and conform with the requirements of

IEC/EN 60601-1-2, 3rd & 4th edition, nevertheless, special precautions may need to be observed:

The Mascot products are suitable for use in Domestic, Residential, Office and Hospital environment, except in special locations where EM Disturbances are known to be high, such as near High Frequency Surgical Equipment or Magnetic Resonance Imaging systems.

When used according to its specification the User can expect the product to fulfil its essential performance, being powering Medical Electrical Devices or charging batteries for Medical Electrical Devices.

**WARNING: Use of this equipment adjacent to or stacked with other equipment should be avoided because it may result in improper operation. If such use is necessary, this equipment and the other equipment should be observed to verify that they are operating normally.**

**WARNING: Use of accessories, transducers and cables other than provided by the manufacturer could result in increased electromagnetic emissions or decreased electromagnetic immunity of this equipment and result in improper operation.**

**WARNING: Portable RF communications equipment should be used no closer than 30 cm (12 inches) to any part of the power supply or battery charger, including cables. Otherwise, degradation of the performance of this equipment could result.**

Guidance and manufacturer's declaration

The Mascot products are intended for use in the electromagnetic environment specified below. The customer or user should ensure that it is used in such an environment.

Test / Standard	Compliance level	Guidance
Emission:		
RF emissions, CISPR 11	Group 1, Class B	Suitable for use in all establishments, including domestic establishments and those directly connected to the public low-voltage power supply network that supplies buildings used for domestic purposes. RF emissions not likely to cause any interference in nearby electronic equipment. However, a separation distance of 30 cm shall be maintained.
Harmonic emissions, IEC 61000-3-2	-	
Voltage fluctuations / flicker emissions, IEC 61000-3-3	-	

Test / Standard	Compliance level	Guidance
Immunity:		
Electrostatic discharge (ESD), IEC 61000-4-2	± 8 kV contact ± 15 kV air	Temporary loss of function may be experienced while the product is subject to the phenomena. The product is expected to recover to it's normal operation.
Electrostatic fast transient / burst, IEC 61000-4-4	± 2 kV for AC-power lines ± 1 kV for output lines	
Surge, IEC 61000-4-5	± 1 kV line to line ± 2 kV line to earth (if applicable).	
Voltage dips, short interruptions and voltage variations on power supply lines, IEC 61000-4-11	<5% $U_T$ (0.5 cycle) 40% $U_T$ (5 cycles) 70% $U_T$ (25 cycles) <5% $U_T$ for 5 s $U_T$ = AC Input Voltage prior to test.	
Power frequency magnetic field IEC 61000-4-8	3 A/m (50/60 Hz)	Not applicable for non-magnetic field sensitive devices.
Conducted RF, IEC 61000-4-6	3 Vrms 150 kHz to 80 MHz	Temporary loss of function may be experienced while the product is subject to the phenomena. The product is expected to recover to it's normal operation.
Radiated RF, IEC 61000-4-3	3V/m for Professional healthcare environment. 10 V/m for Home Healthcare environment. 80 MHz to 2.7 GHz	
<p>These guidelines may not apply in all situations. Electromagnetic propagation is affected by absorption and reflection from structures, objects and people and field strengths from fixed transmitters, such as base stations for radio (cellular/cordless) telephones and land mobile radios, amateur radio, AM and FM radio broadcasts and TV broadcasts cannot be predicted theoretically with accuracy.</p> <p>To assess the electromagnetic environment due to fixed RF transmitters an EM site survey may be considered. If the measured field strength in the location exceeds the applicable RF compliance level above, the Mascot product should be observed to verify normal operation. If abnormal performance is observed, additional measures may be necessary, such as re-orienting or relocating the product.</p>		



## Technical data

(If not appearing in table see marking on the product)

	5V	6V	7.5V	9V	12V	15V	16V	18V	24V	30V	36V
3523	4-5V 2.4A	5.1-6V 2A	6.1-7.5V 1.6A	8.5-9V 1.33A	9.1-12V 1.33A	14-15V 1.06A	N.A	15.1-18V 0.88A	19-24V 0.66A	N.A	N.A
	3A	2.5A	2A	2.5A	2.33A	1.86A	N.A	1.55A	1.16A	N.A	N.A
3626	5-5.9V 4-3.38A	6-7.4V 3.33- 2.7A	7.5-7.9V 3.73- 3.54A	8.5-11.9V 3.11- 2.35A	12-14.9V 2.33-1.87A	15-17.9V 1.86- 1.56A	N.A	18-19.9V 1.55- 1.4A	20-26V 1.16- 1.07A	N.A	N.A
	100-240Vac 50-60Hz	4-5V 5.1-6V	6.1-7.5V	8.5-9V	9.1-12V	14-15V	N.A	15.1-18V	19-24V	N.A	N.A
3020	N.A	8A	7A	6A	5A	N.A	3.75A	N.A	2.5A	2A	N.A
3021											
3823	5-5.9V 2.4-2.0A	6-7.0V 2.0-1.71A	7.1-9.0V 1.71- 1.33A	9.1-10.0V 1.33- 1.2A	10.1-14.9V 1.6-1.06A	15-16.9V 1.06- 0.94A	N.A	17-19.9V 0.94- 0.8A	20-29.9V 0.8-0.53A	N.A	N.A
	220-240Vac 50Hz Max.2.0A	N.A	N.A	N.A	12V+/-2V 17A cont. 20A interm. 265W	N.A	N.A	N.A	24V+/-4V 10A cont. 265W	N.A	N.A
3520	N.A	N.A	N.A	N.A	12V+/-2V 17A cont. 240W	N.A	N.A	N.A	24V+/-4V 10A cont. 240W	N.A	N.A
	115Vac 50-60Hz Max.3.7A	N.A	N.A	N.A	N.A	N.A	N.A	N.A	N.A	N.A	N.A
3320	5V 8A 40W	5.1-6V 6.66A 40W	6.1-7.9V 7.0A 53W	8-11.9V 6.0A 54W	12-14.9V 5.0A 60W	15-16.9V 4.0A 60W	N.A	17-19.9V 3.33A 60W	20-29.9V 2.50A 60W	N.A	30-45V 1.66A 60W
	100-240Vac 50-60Hz max. 1.5A	5V 5A 40W	6.1-7.9V 4A 30W	8-11.9V 4.6A 42W	12-14.9V 3.5A 42W	15-16.9V 2.8A 42W	N.A	17-19.9V 2.33A 42W	20-29.9V 1.75A 42W	N.A	N.A
3721	5V 5A 25W	5.1-6V 4.17A 25W	6.1-7.9V 4A 30W	8-11.9V 4.6A 42W	12-14.9V 3.5A 42W	15-16.9V 2.8A 42W	N.A	17-19.9V 2.33A 42W	20-29.9V 1.75A 42W	N.A	N.A
	100-240Vac 50-60Hz max. 1A	5V 5A 25W	6.1-7.9V 4A 30W	8-11.9V 4.6A 42W	12-14.9V 3.5A 42W	15-16.9V 2.8A 42W	N.A	17-19.9V 2.33A 42W	20-29.9V 1.75A 42W	N.A	N.A

## Technical data

(If not appearing in table see marking on the product)

	Input voltage	5V	6V	7.5V	9V	12V
3825(P) 3825B(P)	100-240Vac 50-60Hz max. 0.25A	4.5V-5.5V max 1.0A max 5.5W	5.51V-6.5V max. 1.0A max 6.5W	6.51V-8.0V 1.0A-0.9A max 7.2W	8.01V-10.0V 0.9A-0.72A max 7.2W	10.01V-12.5V 0.72A-0.57A max 7.2W

	Input voltage	5V	6V	9V	12V	13.2V	16V	24V	36V	48V	60V
2220(P) 2221(P)	100-240Vac 50-60Hz max. 0.35A	N.A	4V-8V max.1.3A 11.7W	N.A	8V-15V 1.3A-1.05A 15.8W	N.A	12V-20V 1.3A-0.8A 16W	20V-28V 0.8A-0.58A 16.2W	28V-40V 0.58A-0.41A 16.4W	40V-52V 0.41A-0.31A 16.4W	52V-64V 0.31A-0.25A 16.1W
2924 2925 2926		N.A	1.5A	1.5A	N.A	1.2A	1A	0.65A	N.A	0.33A	N.A
2720 2721	100-240Vac 50-60Hz	3.5A	5A	3A	N.A	3A	2.5A	N.A	N.A	N.A	N.A
2020 2021 2022		N.A	N.A	4.5A	N.A	4.5A	3.75A	2.5A	N.A	N.A	N.A

	Input voltage	12V	18V	24V	30V	36V	42V	48V
3820	100-240Vac 50-60Hz	12V-14.9V 8.33A - 6.71A	15V - 20.9V 8A - 5.74A	21V - 26.9V 5.71A - 4.46A	27V - 32.9V 4.44A - 3.64A	33V - 38.9V 3.63A - 3.08A	39V - 44.9V 3.07A - 2.67A	45V - 50V 2.66A - 2.4A

(P) = 2MOPP version  
 (B) =Special open frame PCB  
 (All standard versions are also available as open frame units)

## Technical data

(If not appearing in table see marking on the product)

	Input voltage	5V	7V	9V	12V	16V	24V	28V	36V	48V	60V	64V
2820(P)	220-240Vac 50-60Hz max. 1.2A	4-6V	N.A	6-9V 8.5A 77W	9-13.2V 8.5A-7.8A 103W	12-16.8V 8.5A-6.1A 102W	16.8-24V 7.5A-4.2A 101W	24-28V 4.4A-3.8A 106W	28-38V 3.6A-2.7A 103W	38-48V 2.7A-2.1A 103W	55-63V 1.8A-1.6A 101W	63-67V 1.6A-1.5A 100W
2821(P)		4-6V	N.A	6-9V 8.5A 77W	9-13.2V 8.5A-7.8A 103W	12-16.8V 8.5A-6.1A 102W	16.8-24V 7.5A-4.2A 101W	24-28V 4.4A-3.8A 106W	28-38V 3.6A-2.7A 103W	38-48V 2.7A-2.1A 103W	55-63V 1.8A-1.6A 101W	63-67V 1.6A-1.5A 100W
2822(P)		4-6V	N.A	6-9V 8.5A 77W	9-13.2V 8.5A-7.8A 103W	12-16.8V 8.5A-6.1A 102W	16.8-24V 7.5A-4.2A 101W	24-28V 4.4A-3.8A 106W	28-38V 3.6A-2.7A 103W	38-48V 2.7A-2.1A 103W	55-63V 1.8A-1.6A 101W	63-67V 1.6A-1.5A 100W
2840(P)		4-6V	N.A	6-9V 8.5A 77W	9-13.2V 8.5A-7.8A 103W	12-16.8V 8.5A-6.1A 102W	16.8-24V 7.5A-4.2A 101W	24-28V 4.4A-3.8A 106W	28-38V 3.6A-2.7A 103W	38-48V 2.7A-2.1A 103W	55-63V 1.8A-1.6A 101W	63-67V 1.6A-1.5A 100W
2841(P)	4-6V	N.A	6-9V 8.5A 77W	9-13.2V 8.5A-7.8A 103W	12-16.8V 8.5A-6.1A 102W	16.8-24V 7.5A-4.2A 101W	24-28V 4.4A-3.8A 106W	28-38V 3.6A-2.7A 103W	38-48V 2.7A-2.1A 103W	55-63V 1.8A-1.6A 101W	63-67V 1.6A-1.5A 100W	
2842(P)	4-6V	N.A	6-9V 8.5A 77W	9-13.2V 8.5A-7.8A 103W	12-16.8V 8.5A-6.1A 102W	16.8-24V 7.5A-4.2A 101W	24-28V 4.4A-3.8A 106W	28-38V 3.6A-2.7A 103W	38-48V 2.7A-2.1A 103W	55-63V 1.8A-1.6A 101W	63-67V 1.6A-1.5A 100W	
3520	220-240Vac 50-60Hz max. 2A				9-13.2V 17A cont. 20A interm. 264W		16.8-24V 15.5A-10A 260W					
3220(P)	110- 120Vac / 220-240Vac 50-60Hz max. 2.1A	4-6V		6-9V	9-13.2V		16.8-24V	24-28V	28-38V	38-48V	55-63V	63-67V
3221(P)		4-6V		6-9V	9-13.2V		16.8-24V	24-28V	28-38V	38-48V	55-63V	63-67V
3222(P)		4-6V		6-9V	9-13.2V		16.8-24V	24-28V	28-38V	38-48V	55-63V	63-67V
3240(P)		4-6V		6-9V	9-13.2V		16.8-24V	24-28V	28-38V	38-48V	55-63V	63-67V
3240B(P)	4-6V	N.A	N.A	N.A	N.A	N.A	16.8-24V 7.5A-4.2A 101W	24-28V 4.4A-3.8A 106W	28-38V 3.6A-2.7A 103W	38-48V 2.7A-2.1A 103W	55-63V 1.8A-1.6A 101W	63-67V 1.6A-1.5A 100W
2420(P)	100-240Vac	4-6V	6-9V	N.A	9-14.5V	14.5-21.5V	21-34V	N.A	34-44V	44-55V	55-63V	63-67V
2421(P)	50-60Hz	4.5A	4.5A	N.A	4.5A	4.0A-3.3A	2.5A-2.05A	N.A	2.05A-1.6A	1.6A-1.25A	1.25A-1.1A	1.1A-1A
2422(P)	max. 1.6A	27W	41W		55W	69W	70W		70W	72W	69W	67W

(P) = 2MOPP version

(B) = Special open frame PCB

(All standard versions are also available as open frame units)

